

miniRITE Earmold Order Form

For Alpha XT Instruments

☐ RUSH ORDER:

48 hours in-house & next day delivery
(charge applies)

Your Information

Step 1: Ship to Information

Ship to Account:

Account Name:

Address:

City:State:Zip:

Phone #:

Contact Name:

Email (required):

Bill to Account: 6001400

Date:Fitting Date:

Purchase Order #:

Step 2: Patient Information

First Name:

Last Name:

Age:

Medicaid #:

Audiometric Information

Hz:	250	500	1k	2k	3k	4k	6k
AC Right:							
AC Left:							

3. Instrument Information & Identification (only required for Existing Instruments and New Instrument Orders)

☐ New Mold and **New Instrument**

☐ New Mold for **Existing Instrument**

☐ New Mold and New Speaker for **Existing Instrument**

Model:

Serial # (if existing):

Qty:

Style:

Color:

Accessories:

4. Style and product options (Removal String standard for MicroMold, LiteTip and MicroShell)

MICROMOLD
(Solid)

Material	R	L
Hard Acrylic (Transparent)	☐	☐
Soft (See Color/Shore Options)	☐	☐
OtoTherm™ (Transparent)	☐	☐
Retention Styles		
Micro (9mm')	☐	☐
Canal (12mm')	☐	☐
Semi Skeleton	☐	☐
Canal Lock	☐	☐
Skeleton Lock	☐	☐
Half Skeleton	☐	☐
Helix Lock (N/A Soft)	☐	☐
Skeleton Wing Lock (N/A Soft)	☐	☐
Fitting Level		
60	☐	☐
85	☐	☐
Vent Size		
Max Vent	☐	☐
Extra Large >2.4	☐	☐
Large 2.4 (Default)	☐	☐
Medium 1.4	☐	☐
Small 0.8	☐	☐
No vent	☐	☐

LITETIP
(Hollow)

Material	R	L
Hard Acrylic (Transparent)	☐	☐
OtoTherm™ (Transparent)	☐	☐
Retention Styles		
Micro (9mm')	☐	☐
Canal (12mm')	☐	☐
Semi Skeleton	☐	☐
Canal Lock	☐	☐
Skeleton Lock	☐	☐
Half Skeleton	☐	☐
Skeleton Wing Lock	☐	☐
Fitting Level		
60	☐	☐
85	☐	☐
Vent Size		
Max Vent	☐	☐
Extra Large 1.5 (Default)	☐	☐
Large 1.2	☐	☐
Medium 0.7 (short)	☐	☐
Small 0.7 (long)	☐	☐
No vent	☐	☐

MICROSHELL²
(Hard acrylic embedded)

Retention Styles	R	L
Micro (9mm')	☐	☐
Canal (12mm')	☐	☐
Canal Lock	☐	☐
Semi Skeleton	☐	☐
Skeleton Lock	☐	☐
Half Skeleton	☐	☐
Helix Lock	☐	☐
Skeleton Wing Lock	☐	☐
Fitting Level		
60	☐	☐
85	☐	☐
Vent Size		
Max Vent	☐	☐
Extra Large >2.4	☐	☐
Large 2.4 (Default)	☐	☐
Medium Plus 1.8	☐	☐
Medium 1.4	☐	☐
Small 0.8	☐	☐
No vent	☐	☐

POWER RECEIVER MOLD²
(Hard acrylic embedded with removable wire)

Retention Styles	R	L
Canal (12mm')	☐	☐
Canal Lock	☐	☐
Semi Skeleton	☐	☐
Skeleton Lock	☐	☐
Half Skeleton	☐	☐
Helix Lock	☐	☐
Skeleton Wing Lock	☐	☐
Fitting Level		
100	☐	☐
105	☐	☐
Vent Size		
Max Vent	☐	☐
Large 2.4	☐	☐
Medium 1.4 (Default)	☐	☐
Small 0.8	☐	☐
No vent	☐	☐
Removal String for Power Receiver Mold		
☐		

Color options

Soft Material Colors (Shore 40)

☐ Transparent

☐ White

☐ Black

☐ Rose

☐ Orange

☐ Yellow

☐ Green

☐ Red

☐ Blue

Soft Material Colors (Shore 60)

☐ Transparent

☐ Pink

Power Receiver Mold and MicroShell Only

☐ Transparent

☐ Beige

☐ Lt. Brown

☐ Med. Brown

☐ Dk. Brown

☐ Black

☐ Red/Blue (MicroShell Only)

Speaker/Wire Length

R

L

1

2

3

4

Special Instructions:

☐ Order contains contaminated impression. Handlers use gloves.

☐ Please make any changes necessary to fit the receiver size without contacting me.

Please Send: ☐ Impression Boxes ☐ Service Ord. Forms ☐ Return Labels ☐ Return Impressions³

Tip

Consider this style of Mold for the deepest/smallest mold available.

Tip

Consider Semi-Skeleton as a great first option for patients in need of retention (short/narrow canals, difficulty inserting domes). This style provides better retention/stability than canal locks alone and offers better ease of insertion.

¹Approximate length dependent on ear anatomy and impression.

²Only compatible with Alpha XT.

³Impression will be destroyed unless otherwise requested.

⁴N/A with Black color.

⁵N/A with Matte Finish.

Phone: 888.941.4203 | Fax: 732.560.4877 | Bernafon.us

Bernafon

THE SOUND EXPERIENCE