




Starkey | Technical Data

ITE R

In-The-Ear Rechargeable

Fitting Range

- ITE R 50
- ITE R 60
- ITE R 70



Evolv AI 2400 | 2000 | 1600

Color Guide

Faceplate Colors



Shell Colors



2.4 GHz Accessory Compatibility

- TV streamer
- Remote Microphone +
- Remote
- Mini Remote Microphone
- Table Microphone
- Programmer

Patient Features

- IP Rating: 68
- Tinnitus Technology
- Wireless Connectivity
- Rechargeable
- Telecoil

Evolv AI Technology




- Healthable hearing technology with embedded sensors and artificial intelligence

ITE R Gain Data

Measurement	ANSI/IEC 2cc Coupler	IEC OES Coupler
Peak OSPL90 (dB SPL)	115-130	126-139
HFA OSPL90 (dB SPL)	110-123	N/A
RTF OSPL90 (dB SPL)	N/A	119-139
Peak Gain (dB)	50-70	62-80
HFA Full-On Gain (dB)	45-64	N/A
RTF Full-On Gain (dB)	N/A	55-78
Frequency Range (Hz)	<100-8300	<100-9000
Reference Test Freq. (kHz)	N/A	1.6
HFA Frequencies (kHz)	1.0, 1.6, 2.5	N/A
Reference Test Gain (dB)	32-46	45-64
Equivalent Input Noise (dB)	<25	<25
Harmonic Distortion		
500 Hz (%)	<3	<3
800 Hz (%)	<3	<3
1600 Hz (%)	<3	<3
Induction Coil Sensitivity		
HFA SPLITS (ANSI) (dB SPL)	95-108	N/A
MASL (IEC) (dB SPL)	78-96	N/A
Estimated Lithium ION Battery Life		
Li-Ion Rechargeable Battery (hrs)	Up to 24 hours*	
Battery Current (mA)	0.6	0.6
Tinnitus Therapy Stimulus		
Max RMS Output (dB SPL)	87	
Weighted RMS Output Level (dB SPL)	87	
Max 1/3 Octave Output (dB SPL)	87	

Matrices: 115/50, 120/60, 130/70

Battery Size: Encased 312



*Results will vary based on wireless usage.




Starkey | Technical Data

ITE R

In-The-Ear Rechargeable

Fitting Range

- ITE R 50
- ITE R 60
- ITE R 70



Evolv AI 1200 | 1000

Color Guide

Faceplate Colors



Shell Colors



2.4 GHz Accessory Compatibility

- TV streamer
- Remote Microphone +
- Remote
- Mini Remote Microphone
- Table Microphone
- Programmer

Patient Features

- IP Rating: 68
- Tinnitus Technology
- Wireless Connectivity
- Rechargeable
- Telecoil

Evolv AI Technology




- Healthable hearing technology with embedded sensors and artificial intelligence

ITE R Gain Data

Measurement	ANSI/IEC 2cc Coupler	IEC OES Coupler
Peak OSPL90 (dB SPL)	115-130	126-139
HFA OSPL90 (dB SPL)	110-124	N/A
RTF OSPL90 (dB SPL)	N/A	119-139
Peak Gain (dB)	50-70	63-79
HFA Full-On Gain (dB)	45-64	N/A
RTF Full-On Gain (dB)	N/A	55-78
Frequency Range (Hz)	<100-7800	<100-7800
Reference Test Freq. (kHz)	N/A	1.6
HFA Frequencies (kHz)	1.0, 1.6, 2.5	N/A
Reference Test Gain (dB)	32-46	45-64
Equivalent Input Noise (dB)	<25	<25
Harmonic Distortion		
500 Hz (%)	<3	<3
800 Hz (%)	<3	<3
1600 Hz (%)	<3	<3
Induction Coil Sensitivity		
HFA SPLITS (ANSI) (dB SPL)	95-108	N/A
MASL (IEC) (dB SPL)	78-96	N/A
Estimated Lithium ION Battery Life		
Li-Ion Rechargeable Battery (hrs)	Up to 24 hours*	
Battery Current (mA)	0.6	0.6
Tinnitus Therapy Stimulus		
Max RMS Output (dB SPL)	87	
Weighted RMS Output Level (dB SPL)	87	
Max 1/3 Octave Output (dB SPL)	87	

Matrices: 115/50, 120/60, 130/70**

Battery Size: Encased 312



*Results will vary based on wireless usage.

**The highest matrix of 130/70 is not offered on 1000 tier products.






Starkey | Technical Data

ITE R

In-The-Ear Rechargeable

Evolv AI



Latency (ms)	4.3
Attack Time (ms)	8
Release Time (ms)	55