



Starkey | Technical Data

RIC RT

Receiver-In-Canal
Rechargeable with Telecoil

Omega AI

Key Features

- Acoustic Optimization Model 2.0
- Auto Stream
- Status Indicator Light
- Find My Hearing Aids
- Bluetooth® Low Energy Audio with *Auracast™* technology
- StarLink Edge Remote Microphone, StarLink Edge Table Microphone, StarLink Edge TV Streamer & StarLink Remote Control 2.0 Compatibility
- Apple Watch® Controls*
- Balance Assessment within My Starkey App
- Demo Stream
- Tinnitus maskers (blue/red/pink/purple/ocean)
- Lithium-Ion Rechargeable Battery
- 24 Channels
- 4 Programs**
- Directional Processing: Adaptive, Dynamic
- Additive Compressor
- Feedback Cancellor
- Data Log
- Voice AI*
- Translate
- Multiflex Tinnitus Pro
- Transcribe
- Edge Mode+
- Gen AI Smart Assistant & TeleHear AI
- 2-Way Audio & Find My Phone
- Hearing Health & Activity Tracking
- Fall Alert
- Reminders & Self Check
- Auto Sleep
- Tap Control
- SnapFit 2.0 & Custom Cased SnapFit 2.0 Receivers
- TeleHear full remote fit & REM Target Match
- My Starkey & Hear Share App Compatibility
- NOAH Link Wireless Programming

- Telecoil
- CROS System
- Waterproof up to 1 meter
- Wireless programmability

Sound Manager:

- Quiet
- Machine Noise Reduction
- Speech in Noise Reduction
- Transient Noise Reduction
- Wind Reduction
- DNN Directionality
- DNN Spatial Awareness

Ear-to-Ear Technology:

- Binaural Wind
- Binaural Machine
- Binaural Mode Directionality

Multiple Processor:

For many years, Starkey has utilized multiple processors within a single chip, processors that work separately and concurrently to perform the various processing tasks of a modern-day hearing aid. Each processor is optimized to provide efficient calculations for a particular aspect of the audio processing. As technology advances, new types of processors are added, such as those optimized to execute neural networks, so that Starkey can continue to improve the sound quality of our hearing aids and ability of the hearing aid wearer to understand speech in a challenging environment.

SCIF:

All Starkey Omega AI wireless hearing aids are SCIF, compliant devices. All hands-free-bi-directional wireless audio transmission features may be disabled in the hearing firmware through fitting software by the audiologist. Those restricted features cannot be activated by the patient by any means.

*For iOS users only.

**Programs accessible via hearing aid user control or wireless accessory.

Apple Watch® is a trademark of Apple, Inc., registered in the U.S. and other countries and regions. The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. The Auracast™ word mark and logos are trademarks owned by the Bluetooth SIG. Any use of such marks by Starkey is under license. Starkey, TeleHear, Hear Share, Multiflex Tinnitus, Edge Mode, and StarLink are registered trademarks of Starkey Laboratories, Inc. Omega is a trademark of Starkey Laboratories, Inc.

©2025 Starkey Laboratories, Inc. All Rights Reserved. 7/25 SPEC3100-00-EN-GS




Starkey | Technical Data

RIC RT

Receiver-In-Canal
Rechargeable with Telecoil

Fitting Range

- L
- M
- P



Omega AI

Color Guide

Standard Colors






Patient Features

- IP Rating: 68
- Tinnitus Technology
- Wireless Connectivity
- Rechargeable Battery
- Telecoil
- CROS System
- Dual Radio (2.4 GHz + NFMI)
- Status Indicator Light

Omega AI Technology

- Personal health monitoring technology with embedded sensors and artificial intelligence
- Compatible with StarLink Remote Control 2.0 and StarLink Edge accessories

	L	M	P	Matrices: L, M, P Battery: Lithium-ion
Measurement	ANSI/IEC 2cc Coupler	ANSI/IEC 2cc Coupler	ANSI/IEC 2cc Coupler	
Peak OSPL90 (dB SPL)	107	117	120	
HFA OSPL90 (dB SPL)	102	114	117	
Peak Gain (dB)	42	50	60	
HFA Full-On Gain (dB)	36	47	56	
Frequency Range (Hz)	<100-9400	<100-9500	<100-9200	
HFA Frequencies (kHz)	1.0,1.6,2.5	1.0,1.6,2.5	1.0,1.6,2.5	
Reference Test Gain (dB)	25	37	40	
Equivalent Input Noise (dB SPL) <i>Expansion On (Default)</i>	15	15	15	
Equivalent Input Noise (dB SPL) <i>Expansion Off</i>	24	24	24	
Harmonic Distortion				
500 Hz (%)	<3	<3	<3	
800 Hz (%)	<3	<3	<3	
1600 Hz (%)	<3	<3	<3	
Induction Coil Sensitivity				
HFA SPLITS (ANSI) (dB SPL)	84	94	98	
MASL (IEC) (dB SPL)	67	79	86	
Estimated Lithium-ion Battery Life*				
Without streaming (hrs)	Up to 51	Up to 51	Up to 51	
With streaming (hrs)	Up to 45	Up to 45	Up to 45	
Battery Current (mA)	0.6	0.6	0.6	
Tinnitus Therapy Stimulus				
Max RMS Output (dB SPL)	87	87	87	
Weighted RMS Output Level (dB SPL)	87	87	87	
Max 1/3 Octave Output (dB SPL)	87	87	87	



*Results will vary based on wireless usage.

Starkey and StarLink are registered trademarks of Starkey Laboratories, Inc. Omega is a trademark of Starkey Laboratories, Inc.
©2025 Starkey Laboratories, Inc. All Rights Reserved. 7/25 SPEC3100-00-EN-GS




Starkey | Technical Data

RIC RT CUSTOM CASED

Receiver-In-Canal
Rechargeable with Telecoil

Fitting Range

- L
- M
- P
- UP



Omega AI

Color Guide

Standard Colors



Patient Features

- IP Rating: 68
- Tinnitus Technology
- Wireless Connectivity
- Rechargeable Battery
- Telecoil
- CROS System
- Dual Radio (2.4 GHz + NFMI)
- Status Indicator Light

Omega AI Technology

- Personal health monitoring technology with embedded sensors and artificial intelligence
- Compatible with StarLink Remote Control 2.0 and StarLink Edge accessories

	L	M	P	UP	Matrices: L, M, P, UP Battery: Lithium-ion
Measurement	ANSI/IEC 2cc Coupler	ANSI/IEC 2cc Coupler	ANSI/IEC 2cc Coupler	ANSI/IEC 2cc Coupler	
Peak OSPL90 (dB SPL)	107	117	120	125	
HFA OSPL90 (dB SPL)	102	114	117	122	
Peak Gain (dB)	42	50	60	67	
HFA Full-On Gain (dB)	36	47	56	65	
Frequency Range (Hz)	<100-9400	<100-9500	<100-9200	<100-5800	
HFA Frequencies (kHz)	1.0,1.6,2.5	1.0,1.6,2.5	1.0,1.6,2.5	1.0,1.6,2.5	
Reference Test Gain (dB)	25	37	40	45	
Equivalent Input Noise (dB SPL) Expansion On (Default)	15	15	15	15	
Equivalent Input Noise (dB SPL) Expansion Off	24	24	24	24	
Harmonic Distortion					
500 Hz (%)	<3	<3	<3	<3	
800 Hz (%)	<3	<3	<3	<3	
1600 Hz (%)	<3	<3	<3	<3	
Induction Coil Sensitivity					
HFA SPLITS (ANSI) (dB SPL)	84	94	98	105	
MASL (IEC) (dB SPL)	67	79	86	94	
Estimated Lithium-ion Battery Life*					
Without streaming (hrs)	Up to 51	Up to 51	Up to 51	Up to 51	
With streaming (hrs)	Up to 45	Up to 45	Up to 45	Up to 45	
Battery Current (mA)	0.6	0.6	0.6	0.6	
Tinnitus Therapy Stimulus					
Max RMS Output (dB SPL)	87	87	87	87	
Weighted RMS Output Level (dB SPL)	87	87	87	87	
Max 1/3 Octave Output (dB SPL)	87	87	87	87	

*Results will vary based on wireless usage.

Starkey and StarLink are registered trademarks of Starkey Laboratories, Inc. Omega is a trademark of Starkey Laboratories, Inc.
©2025 Starkey Laboratories, Inc. All Rights Reserved. 7/25 SPEC3100-00-EN-GS



Starkey | Technical Data

RIC RT

Receiver-In-Canal
Rechargeable with Telecoil










Starkey | Technical Data

RIC RT CUSTOM CASED

Receiver-In-Canal
Rechargeable with Telecoil

Omega AI



Latency (ms) 4.3

Attack Time (ms) 3

Release Time (ms) 60




Starkey | Technical Data

RIC RT CUSTOM CASED

Receiver-In-Canal
Rechargeable with Telecoil

Fitting Range

● UP-



Omega AI

Color Guide

Standard Colors



Patient Features

- IP Rating: 68
- Tinnitus Technology
- Wireless Connectivity
- Rechargeable Battery
- Telecoil
- CROS System
- Dual Radio (2.4 GHz + NFMI)
- Status Indicator Light

Omega AI Technology

- Personal health monitoring technology with embedded sensors and artificial intelligence
- Compatible with StarLink Remote Control 2.0 and StarLink Edge accessories

UP-

Matrices: UP-

Battery: Lithium-ion

Measurement

ANSI/IEC
2cc Coupler

Peak OSPL90 (dB SPL)	120
HFA OSPL90 (dB SPL)	116
Peak Gain (dB)	64
HFA Full-On Gain (dB)	60
Frequency Range (Hz)	<100-5800

HFA Frequencies (kHz)	1.0, 1.6, 2.5
Reference Test Gain (dB)	39

Equivalent Input Noise (dB SPL) <i>Expansion On (Default)</i>	15
Equivalent Input Noise (dB SPL) <i>Expansion Off</i>	24

Harmonic Distortion

500 Hz (%)	<3
800 Hz (%)	<3
1600 Hz (%)	<3

Induction Coil Sensitivity

HFA SPLITS (ANSI) (dB SPL)	98
MASL (IEC) (dB SPL)	91



Estimated Lithium-ion Battery Life*

Without streaming (hrs)	Up to 51
With streaming (hrs)	Up to 45
Battery Current (mA)	0.6

Tinnitus Therapy Stimulus

Max RMS Output (dB SPL)	87
Weighted RMS Output Level (dB SPL)	87
Max 1/3 Octave Output (dB SPL)	87

Latency (ms)	4.3
Attack Time (ms)	3
Release Time (ms)	60



*Results will vary based on wireless usage.

Starkey and StarLink are registered trademarks of Starkey Laboratories, Inc. Starkey Omega is a trademark of Starkey Laboratories, Inc.
©2025 Starkey Laboratories, Inc. All Rights Reserved. 7/25 SPEC3100-00-EN-GS